


RG11

RG-Cables acc. to MIL-C-17F and MIL-C-17G



Application

Standards

acc. to MIL-C-17F and MIL-C-17G

Flame resistance

acc. to IEC 60332-1

Construction RG11 2YCY 1.2Lz/7.25

Inner conductor	stranded copper wires, tinned, diameter 7 x 0.39
Insulation	PE, diameter 7.25 ± 0.05 mm
Braid	bare copper wires, 96% optical coverage
Sheath	PVC, diameter 10.1 ± 0.2 mm

Construction RG11 + 2nd braid 2YCYCY 1.2Lz/7.25

Inner conductor	stranded copper wires, tinned, 7 x 0.39 mm, diameter 1.17
Insulation	PE, diameter 7.25 ± 0.05 mm
1 st braid	bare copper wires, 96% optical coverage
1 st sheath	PVC, diameter 10.1 ± 0.2 mm
2 nd braid	bare copper wires, 93.5% optical coverage
2 nd sheath	PVC, diameter 13.5 ± 0.5 mm

Mechanical properties

Minimum bending radius	without load	5 x outer diameter
	with load	10 x outer diameter
Temperature	during operation	-40° C to + 85° C
	during installation	-15° C to + 55° C

RG11

Electrical properties

at 20°C

DC resistance	Inner conductor	21 Ω/km
	1 st braid	4.0 Ω/km
	2nd braid (only RG11 + 2nd braid)	3.6 Ω/km
Mutual capacitance		67 nF/m
Characteristic impedance		75 Ω ± 3 Ω
Velocity ratio		66 %
Operating voltage		≤ 3.6 kV _{rms}
Test voltage	Inner/Outer conductor	7.6 kV _{rms}
	Between braids (only RG11 + 2nd braid)	2.0 kV _{rms}

Electrical data

at 20°C

Frequency (MHz)	Attenuation (dB/100m)	Max. power rating (Watts) (ambient temperature 25°C and max. inner conductor temperature 70°C)
10	1.8	2800
100	6.5	810
200	9.8	450
400	14.1	370
800	22.5	130
1000	25.2	110

All other requirements acc. to MIL-C-17F respectively MIL-C-17G

Technical data

Product code	Designation	Type	Brand name	Outer diameter	Weight	Standard delivery length	Drum size	Gross weight	Copper content	Tensile force
				mm	kg/km	m	*PWD/**O WD	kg		N
1002715	2YCY	1.2Lz/7.25	M17/6- RG11	10.1	135.2	1000	*760/360/42 0	147	62.6	345
1002707	2YCYCY	1.2Lz/7.25 (+ 2nd braid)	M17/6- RG11 (+ 2 nd braid)	13.5	270	1000	**1000/500/ 560	324	139.9	765

*PWD (Plywood drum)

**OWD (One way drum)

RG11**Product Code Table**

Product Description	Product Code	PG Reference Code	PG Part Number
DR RG11 75-COAX 1.17/7.25PVC BK 500DW	1002715-00500DW	60017534	60017534

© PRYSMIAN GROUP 2008, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.