





# **IP54 Wall Mounted Cabinet with Swing Frame**

Prysmian Part Numbers: See below





A range of Wall Mounted Cabinets with a swing out frame sealed to IP54. The cabinets are supplied with 19" mounting rails on an internal swing out frame to provide access for cable routing and to internal equipment. The cabinets have a lockable steel framed acrylic glass door for safety and security. The cabinets are available in heights of 380mm, 600mm and 760mm (6U, 11U and 14U).

### **Features and Benefits**

- Cabinet is 600mm in width and 300mm in depth.
- The cabinet is available in three different heights of 380mm, 600mm and 760mm. The usable internal height in units is 6U, 11U and 14U.
- The cabinets have a swing out frame for ease of cable routing and to provide access to equipment.
- Supplied with 19" mounting rails and can accommodate a range of 19" products including the Prysmian SRS3000 Splice Only, Patch Only, Splice and Patch and Storage shelves.
- Simple one man installation. Supplied completely assembled.
- Supplied with a lockable transparent acrylic door, or with a steel door.
- The cabinet is sealed to IP54.
- Heavy duty construction.
- Painted light grey RAL 7035.

#### **Kit Contents**

• The cabinet is supplied with side panels left and right, a set of 19" mounting rails. cage nuts and a lockable glass door.

#### **Part Numbers**

- XCPSC01348 6U Transparent Door
- XCPSC01349 11U Transparent Door
- XCPSC01350 14U Transparent Door
- XCPSC01825 6U Steel Door
- XCPSC01826 11U Steel Door
- XCPSC01827 14U Steel Door





### **Wall Mounted Products**



### **Technical Data**

• Height (U): 6, 11 or 14

• Dimensions (mm): 6U: (h) 380 x (w) 600 x (d) 330

11U: (h) 600 x (w) 600 x (d) 330 14U: (h) 760 x (w) 600 x (d) 330

• Operating temperature: -20°C to + 60°C (5 to 95% RH)

• Material:

• Enclosure: Sheet Steel 1.5mm

• Swing Frame: Sheet Steel

• Front Door: Extruded Aluminium and Acrylic (Transparent Door)

Sheet Steel (Steel Door)


• Finish:


Enclosure: Powder Coated Paint Grey RAL 7035
 Swing Frame: Powder Coated Paint Grey RAL 7035

• Front Door: Anodized, Aluminium Silver (Transparent door)

Powder Coated Paint Grey RAL 7035 (Steel Door)

• Sealing: IP54 to IEC 60-529






## **Logistics**

• Packing Dimensions (mm):

6U: (h) 420 (w) 640 (d) 370
11U: (h) 640 (w) 640 (d) 370
14U: (h) 800 (w) 640 (d) 370
Weight (Kg): (6U) 16 (11U) 25 (14U) 31



Model		Height mm					
	U (HE)	H1	H2	Н3	Н4	H5	Н6
XCPSC01348 XCPSC01825	6	380	330	320	222	377	317
XCPSC01349 XCPSC01826	11	600	545	542	445	597	537
XCPSC01350 XCPSC01827	14	760	705	676	578	757	697

Please contact your local sales office listed on www.prysmiangroup.com

© Prysmian Group 2012, All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.

